


ASSISTED SERVICE HEATED DELI - FITTING INSTRUCTIONS

A) WORKTOP CUT-OUT


Model Ref.	Worktop Cut Out Size (mm)		Model Weight
	Length	Width	(in Kg)
HDL2	795	650	85
HDL3	1145	650	102
HDL4	1495	650	118
HDL5	1845	650	128

FIX LIFTING BRACKETS TO FRAME END FLANGES USING SCREWS ALREADY IN FLANGES, THEN LOCATE LIFTING BARS INTO SQUARE HOLES.



FRONT ISOMETRIC (CUSTOMER SIDE)

B) LOCATING OF CONTROL BOX



(CUSTOMER SIDE)

FOR POSITIONING

(OPERATOR SIDE)

Recommended Control Box Positioning
Site the control box preferably to an
upright surface, in an accessible service
void, adjacent to or below the display unit
(minimum clearance below underside
of display unit = 200mm).

Incorrect Control Box Positioning
The control box must not be located

- directly to the underside of the display unit,
- 2) above a hot cupboard or,
- 3) where ambient temperature is above 40°C,
- where likely to allow ingress of water i.e. wet floor areas.


(OPERATOR SIDE)

* D) FOR MODELS ABOVE 3kW

INCOMING ELECTRICAL SUPPLY DETAILS

Model Ref.	Current	Voltage	Power
HDL4	20A	230V	3.8kW
HDL5	32A	230V	4.8kW

INCOMING ELECTRICAL SUPPLY (SEE TABLE ABOVE FOR SUPPLY DETAILS)



CLOSE-UP OF INCOMING WIRING DETAIL


INSIDE LAYOUT OF CONTROL BOX





Tel. 01254 238 282 Fax. 01254 238 228 e-mail: aftersales@cedlimited.com





(BY OTHERS)