

SELF HELP CHILLED PATISSERIE (FIXED BACK) - R290 WITH AIRFLOW KIT PAF2 (IN/OUT TO OPERATOR SIDE)

FITTING INSTRUCTIONS



General Installation Considerations


- 1) Area in which display is to be sited must have a minimum 2) Install over a sealed floor or ventilated floor void. room floor area no less than 17 sq m (KPC6FBHTD),

- Display will operate in a 24 hour environment.
- 26 sq m (KPC9FBHTD), 28 sq m (KPC12FBHTD) or 29 sq m (KPC15&18FBHTD). 4) Do not site the display beneath a high level of direct sunlight.
 - 3) Do not site the display within 2m of ceiling mounted air conditioning grilles. 6) Access to maintain condensing unit should be made via removable
 - fascia panels or doors to customer and operator side of counter.

A) WORKTOP CUT-OUT


Model Ref.	Worktop Cut Out Size (mm)		Model Weight
	Length	Width	(in Kg)
KPC6FBHTD+PAF2	570	740	146
KPC9FBHTD+PAF2	870	740	193
KPC12FBHTD+PAF2	1170	740	245
KPC15FBHTD+PAF2	1470	740	299
KPC18FBHTD+PAF2	1770	740	351

FIX LIFTING BRACKETS TO FRAME END FLANGES USING SCREWS ALREADY IN FLANGES, THEN LOCATE LIFTING BARS INTO SQUARE HOLES.




FLEXIBLE DUCTING & IN-LINE FAN SUPPLIED LOOSE. RE-ATTACH FLEXIBLE DUCTING & IN-LINE FAN TO SIDE OF COMPRESSOR CRADLE ONCE UNIT HAS BEEN DROPPED INTO PLACE. ELECTRICALY CONNECT FAN TO CONTROL BOX WITH "KETTLE PLUG"

FRONT ISOMETRIC (CUSTOMER SIDE)



C) FITTING INTO COUNTER WORKTOP

E) AIR INTAKE TUNNEL / PLENUM FITTING (OPERATOR SIDE FASCIA PANEL)



INTAKE CUT-OUT, TO STOP THE RE-CIRCULATION OF HOT AIR FROM THE COMPRESSOR. SILICON SEAL AROUND EDGES TO ENSURE THERE ARE NO AIR GAPS.

D) FITTING SHELVES




LOCATE SHELF SUPPORT BRACKETS INTO REAR SLOTS AT HEIGHT & ANGLE TO SUIT PRODUCTS (NOTE: 2 No. BRACKETS WITH GLASS STOPS TO BE FITTED AT BTM.). PUSH ON 3 x GREY SILICON SHELF RESTS ONTO EACH BRACKET BEFORE GLASS SHELVES ARE LOWERED ON (NOTE: 1 No. SHORT SHELF TO BE FITTED AT BTM.)

F) FITTING OF LOUVRE GRILLES

KIT LOUVRE GRILLE

(1 SUPPLIED WITH KIT)





Tel. 01254 238 282 Fax. 01254 238 228 e-mail: aftersales@cedlimited.com



FLOW KIT GRILLE

(SUPPLIED BY CED)

REMOVABLE FASCIA PANEL;

LIFT-OFF SERVICE COVER

OR HINGED DOOR

(BY OTHERS)

REMOVABLE FASCIA PANEL LIFT-OFF SERVICE COVER OR HINGED DOOR (BY OTHERS) REAR STANDARD STAINLESS STAINLESS STEEL AIR STEEL AIR GRILLE (SUPPLIED BY CED)

REMOVE LIFTING BRACKETS AFTER FITTING AND REPLACE

SCREWS INTO FRAME **END FLANGES**

> **ISOMETRIC** (OPERATOR SIDE)

SILICON SEAL AROUND

DISPLAY FLANGE TO

COUNTER WORKTOP

PLENUM OR **4 SIDED TUNNEL**

(BY OTHERS)